

Eaton D04403

Catalog Number: D04403

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 460 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 575Y/332V, 150°C, 14 kVA, Al windings, Frame: 912B, uses WS38



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Drive isolation ventilated transformer	D04403
	UPC
	786680332029
Product Length/Depth	Product Height
16.5 in	30 in
Product Width	Product Weight
23 in	220 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

912B

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Horsepower

10 hp

Kva Rating

14 kVA

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

575Y/332 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - D04403](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)