

Eaton D2CB12 15

Catalog Number: D2CB12 15

Eaton Crouse-Hinds series D2CB replacement circuit breaker assembly, 15A, Copper-free aluminum, Two-pole, Factory sealed, 120/240 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series D2CB replacement circuit breaker assembly	D2CB12 15
	UPC
	782274302829
Product Length/Depth	Product Height
7 in	4.25 in
Product Width	Product Weight
2.5 in	2.73 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 2

Product specifications

Number Of Poles

Two-pole

Amperage Rating

15A

Voltage rating

120 Vac/240 Vac

Material

Copper-free aluminum

Special features

Factory sealed

Resources

Catalogs

[D2PB Series Circuit Breaker Panelboards catalog page](#)

Certification reports

[D2PB Hazardous Area Circuit Breaker Panelboards UL certification](#)

Installation instructions

[IF 908 - D2CB Circuit Breaker Assembly](#)

Specifications and datasheets

[Eaton Specification Sheet - D2CB12 15](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)