

Eaton DBR56731 WT60 3

Catalog Number: DBR56731 WT60 3

Eaton Crouse-Hinds series Arktite DBR interlocked receptacle, 60A, 60A circuit breaker, Three-wire, three-pole, Brass contacts, With breaker, Style 1, Cutler-Hammer, Copper-free aluminum, Spring door, 1-1/2", 600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite DBR interlocked receptacle	DBR56731 WT60 3
	UPC
	782274278261
Product Length/Depth	Product Height
7.25 in	22.75 in
Product Width	Product Weight
8.13 in	0.031 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

9

12

Product specifications

Enclosure type

With breaker

Receptacle style

Spring door

Amperage Rating

60A

Grounding style

Style 1

Configuration

Three-wire, three-pole

Voltage rating

600 Vac

Trade size

1-1/2"

Circuit breaker amperage

60A

Manufacturer

Cutler-Hammer

Material

Copper-free aluminum

Contact material

Brass

Resources

Catalogs

[Arktite DBR Dust-Ignitionproof Interlock Receptacles catalog page](#)

Certification reports

[Arktite DBR Dust-Ignitionproof Interlock Receptacles with Enclosed Circuit Breakers UL certification](#)

Installation instructions

[IF 1181 - DBR Interlock Receptacle](#)

Specifications and datasheets

[Eaton Specification Sheet - DBR56731 WT60 3](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)