

Eaton DCG1102UPM

Catalog Number: DCG1102UPM

Eaton heavy duty DC disconnect,60A,NEMA 4,Painted steel,Non-fusible,Grounded,#14-#2 AWG lug capacity, #14-#2 AWG solid return,1,Isolated return,DC photovoltaic systems,1000 Vdc

General specifications

Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCG1102UPM

UPC

786685557700

Product Length/Depth

10.22 in

Product Height

14.14 in

Product Width

8.76 in

Product Weight

21 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 98B
NEC 690 per UL 1741

Catalog Notes

Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.



defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

60 A

Number of circuits

1

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 4

Protection

Non-fusible

Application

Solar

Main lug wire size

#14-#2 AWG lug capacity, #14-#2 AWG solid return

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Isolation

Isolated return

Switch type

Heavy duty

DC photovoltaic systems

Resources

Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

Multimedia

Switching Devices Flex Center

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DCG1102UPM

Protection

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)