

Eaton DCG1104FXM

Catalog Number: DCG1104FXM

Eaton heavy duty DC disconnect,200A,NEMA 4x,Grade 316 stainless steel,Fusible,Grounded,LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14,1,Isolated return,DC photovoltaic systems,1000 Vdc



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG1104FXM
UPC	Product Length/Depth
786685625454	35.38 in
Product Height	Product Width
11.63 in	16.54 in
Product Weight	Warranty
45 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

NEC 690 per UL 1741
UL 98B

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

200 A

Number of circuits

1

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 4X

Protection

Fusible

Application

Solar

Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

316 stainless steel

Fuse configuration

Fusible

Isolation

Isolated return

Switch type

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG1104FXM](#)

Heavy duty
DC photovoltaic systems

Protection

Fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)