

Eaton DCG1105FPM

Catalog Number: DCG1105FPM

Eaton heavy duty DC disconnect,400A,NEMA 4,Painted steel,Fusible,Grounded,1,Isolated return,DC photovoltaic systems,1000 Vdc



General specifications

Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCG1105FPM

UPC

786685866062

Product Length/Depth

12.42 in

Product Height

57.47 in

Product Width

24.12 in

Product Weight

60 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

400 A

Number of circuits

1

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 4

Protection

Fusible

Application

Solar

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible

Isolation

Isolated return

Switch type

Heavy duty

DC photovoltaic systems

Protection

Fusible

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG1105FPM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)