

# Eaton DCG1105UWM

Catalog Number: DCG1105UWM

Eaton heavy duty DC disconnect,400A,NEMA 4X,Grade 304 stainless steel,Non-fusible,Grounded,1,Isolated return,DC photovoltaic systems,1000 Vdc



## General specifications

### Product Name

Eaton heavy duty DC disconnect

### Catalog Number

DCG1105UWM

### UPC

786685865997

### Product Length/Depth

12.42 in

### Product Height

57.47 in

### Product Width

24.12 in

### Product Weight

60 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

DC disconnect/grounded system

### Amperage Rating

400 A

### Number of circuits

1

### Ground

Grounded

### Maximum voltage

1000 VDC

### NEMA rating

NEMA 4X

### Protection

Non-fusible

### Application

Solar

### System voltage

1000 VDC

### Voltage rating

1000 VDC

### Series

DC photovoltaic applications

### Enclosure

NEMA 4X

### Enclosure material

304 stainless steel

### Fuse configuration

Non-fusible

### Isolation

Isolated return

### Switch type

Heavy duty

DC photovoltaic systems

### Protection

Non-fusible

## Resources

### Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

### Multimedia

Double Up on Safety

Switching Devices Flex Center

### Specifications and datasheets

Eaton Specification Sheet - DCG1105UWM

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)