

Eaton DCG2064UXM

Catalog Number: DCG2064UXM

Eaton heavy-duty DC disconnect,200A,Solar,Grade 316 stainless steel,Non-fusible,Grounded,In/Out(LC): 300 MCM-#6, In/Out(SR): 300 MCM-#6,600 Vdc,NEMA 4X,2,Non-fusible,Isolated return,Two-pole,DC photovoltaic applications,Single-throw



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG2064UXM
UPC	Product Length/Depth
786685624808	35.38 in
Product Height	Product Width
11.63 in	16.54 in
Product Weight	Warranty
45 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

NEC 690 per UL 1741
UL 98B

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

200 A

Number of circuits

2

Ground

Grounded

Maximum voltage

600 VDC

NEMA rating

NEMA 4X

Protection

Non-fusible

Application

Solar

Main lug wire size

In/Out(LC): 300 kcmil-#6, In/Out(SR): 300 kcmil-#6

Number of poles

Two-pole

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

316 stainless steel

Fuse configuration

Non-fusible

Isolation

Isolated return

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG2064UXM](#)

Switch type

DC photovoltaic systems

Heavy duty safety

Single-throw

Protection

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia