

Eaton DCG2101UWM

Catalog Number: DCG2101UWM

Eaton heavy duty DC disconnect,30A,NEMA 4X,Grade 304 stainless steel,Non-fusible,Grounded,#14-#2 AWG lug capacity, #14-#2 AWG solid return,2,Isolated return,DC photovoltaic systems,1000 Vdc



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG2101UWM
UPC	Product Length/Depth
786685557847	10.22 in
Product Height	Product Width
19.08 in	12.88 in
Product Weight	Warranty
37 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
NEC 690 per UL 1741 UL 98B	Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

30 A

Number of circuits

2

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 4X

Protection

Non-fusible

Application

Solar

Main lug wire size

#14-#2 AWG lug capacity, #14-#2 AWG solid return

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Non-fusible

Isolation

Isolated return

Switch type

Heavy duty

DC photovoltaic systems

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG2101UWM](#)

Protection

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)