

# Eaton DCG2101UXM

Catalog Number: DCG2101UXM

Eaton heavy duty DC disconnect,30A,NEMA 4X,Grade 316 stainless steel,Non-fusible,Grounded,#14-#2 AWG lug capacity,#14-#2 AWG solid return,2,Isolated return,DC photovoltaic systems,1000 Vdc



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty DC disconnect	DCG2101UXM
<b>UPC</b>	<b>Product Length/Depth</b>
786685557878	10.22 in
<b>Product Height</b>	<b>Product Width</b>
19.08 in	12.88 in
<b>Product Weight</b>	<b>Warranty</b>
37 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL 98B NEC 690 per UL 1741	Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

## defaultTaxonomyAttributeLabel

### Type

DC disconnect/grounded system

### Amperage Rating

30 A

### Number of circuits

2

### Ground

Grounded

### Maximum voltage

1000 VDC

### NEMA rating

NEMA 4X

### Protection

Non-fusible

### Application

Solar

### Main lug wire size

#14-#2 AWG lug capacity, #14-#2 AWG solid return

### System voltage

1000 VDC

### Voltage rating

1000 VDC

### Series

DC photovoltaic applications

### Enclosure

NEMA 4X

### Enclosure material

316 stainless steel

### Fuse configuration

Non-fusible

### Isolation

Isolated return

### Switch type

Heavy duty

DC photovoltaic systems

## Resources

### Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

### Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

### Specifications and datasheets

[Eaton Specification Sheet - DCG2101UXM](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Protection

Non-fusible



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)