

Eaton DCG2104UWM

Catalog Number: DCG2104UWM

Eaton heavy duty DC disconnect,200A,NEMA 4X,Grade 304 stainless steel,Non-fusible,Grounded,LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14,2,Isolated return,DC photovoltaic systems,1000 Vdc



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG2104UWM
UPC	Product Length/Depth
786685625362	57.47 in
Product Height	Product Width
12.43 in	24.12 in
Product Weight	Warranty
60 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 98B
NEC 690 per UL 1741

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

200 A

Number of circuits

2

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 4X

Protection

Non-fusible

Application

Solar

Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Non-fusible

Isolation

Isolated return

Switch type

Resources

Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

Multimedia

Double Up on Safety

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - DCG2104UWM

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services

Heavy duty
DC photovoltaic systems

Protection

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)