

Eaton DCG2105FRM

Catalog Number: DCG2105FRM

Eaton heavy duty DC disconnect,400A,NEMA 3R,Painted galvanized steel,Fusible,Grounded,2,DC photovoltaic systems,1000 Vdc



General specifications

Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCG2105FRM

UPC

786685866093

Product Length/Depth

12.42 in

Product Height

57.47 in

Product Width

24.12 in

Product Weight

60 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

400 A

Number of circuits

2

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 3R

Protection

Fusible

Application

Solar

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible

Switch type

Heavy duty

DC photovoltaic systems

Protection

Fusible

Resources

Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

Multimedia

Switching Devices Flex Center

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DCG2105FRM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)