

Eaton DCG2105UPM

Catalog Number: DCG2105UPM

Eaton heavy duty DC disconnect,400A,NEMA 4,Painted steel,Non-fusible,Grounded,2,DC photovoltaic systems,1000 Vdc



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG2105UPM
UPC	Product Length/Depth
786685866024	12.42 in
Product Height	Product Width
57.47 in	24.12 in
Product Weight	Warranty
60 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

400 A

Number of circuits

2

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 4

Protection

Non-fusible

Application

Solar

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

DC photovoltaic systems

Protection

Non-fusible

Resources

Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

Multimedia

Switching Devices Flex Center

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DCG2105UPM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)