

Eaton DCG3062UXM

Catalog Number: DCG3062UXM

Eaton heavy-duty DC disconnect, 60 A, NEMA 4X, Grade 316 stainless steel, In/Out(LC): #2-#14 AWG, In/Out(SR): 1/0-#14 AWG, 3 circuits, Non-fusible, Three-pole, 600 Vdc per pole, Wire size: #14-#4 AWG input, #14-#4 AWG output



General specifications

Product Name

Eaton heavy duty DC disconnect

UPC

786685556895

Product Height

19.08 in

Product Weight

21 lb

Certifications

NEC 690 per UL 1741
UL 98B

Catalog Number

DCG3062UXM

Product Length/Depth

10.22 in

Product Width

8.76 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

60 A

Number of circuits

3

Ground

Grounded

Maximum voltage

600 VDC

Protection

Non-fusible

Application

Solar

Main lug wire size

In/Out(LC): #2-#14 AWG, In/Out(SR): 1/0-#14 AWG

Number of poles

Three-pole

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

316 stainless steel

Fuse configuration

Non-fusible

Isolation

Isolated return

Switch type

Single-throw

Heavy duty safety

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG3062UXM](#)

Protection

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)