

Eaton DCG3063FWM

Catalog Number: DCG3063FWM

Eaton heavy-duty DC disconnect, 100 A, NEMA 4X, Grade 304 stainless steel, In/Out(LC/SR): 1/0-#14 AWG, 3 circuits, Fusible, Three-pole, 600 Vdc per pole, Wire size: #14-#4 AWG input, #14-#4 AWG output



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG3063FWM
UPC	Product Length/Depth
786685556871	10.22 in
Product Height	Product Width
24.95 in	11.79 in
Product Weight	Warranty
29 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL 98B NEC 690 per UL 1741	Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

100 A

Number of circuits

3

Ground

Grounded

Maximum voltage

600 VDC

Protection

Fusible

Application

Solar

Main lug wire size

In/Out(LC/SR): 1/0-#14 AWG

Number of poles

Three-pole

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible

Isolation

Isolated return

Switch type

Heavy duty safety

Single-throw

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG3063FWM](#)

Protection

Fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia