

Eaton DCG3104FRM

Catalog Number: DCG3104FRM

Eaton heavy duty DC disconnect,200A,NEMA 3R,Painted galvanized steel,Fusible,Grounded,LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14,3,Isolated return,DC photovoltaic systems,1000 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG3104FRM
UPC	Product Length/Depth
786685625508	35.38 in
Product Height	Product Width
11.63 in	24.46 in
Product Weight	Warranty
75 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 98B
NEC 690 per UL 1741

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

200 A

Number of circuits

3

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 3R

Protection

Fusible

Application

Solar

Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible

Switch type

DC photovoltaic systems

Heavy duty

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG3104FRM](#)

Protection

Fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia