

Eaton DCG3104UPM

Catalog Number: DCG3104UPM

Eaton heavy duty DC disconnect,200A,NEMA 4,Painted steel,Non-fusible,Grounded,LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14,3,Isolated return,DC photovoltaic systems,1000 Vdc

General specifications



Photo is representative

Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCG3104UPM

UPC

786685625393

Product Length/Depth

35.38 in

Product Height

11.63 in

Product Width

24.26 in

Product Weight

80 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 98B

NEC 690 per UL 1741

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

200 A

Number of circuits

3

Ground

Grounded

Maximum voltage

1000 VDC

NEMA rating

NEMA 4

Protection

Non-fusible

Application

Solar

Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

DC photovoltaic systems

Protection

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG3104UPM](#)

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)