

# Eaton DCG3104UXM

Catalog Number: DCG3104UXM

Eaton heavy duty DC disconnect,200A,NEMA 4X,Grade 316 stainless steel,Non-fusible,Grounded,LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14,3,Isolated return,DC photovoltaic systems,1000 Vdc



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty DC disconnect	DCG3104UXM
<b>UPC</b>	<b>Product Length/Depth</b>
786685625416	35.38 in
<b>Product Height</b>	<b>Product Width</b>
11.63 in	24.26 in
<b>Product Weight</b>	<b>Warranty</b>
80 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL 98B  
NEC 690 per UL 1741

## defaultTaxonomyAttributeLabel

### Type

DC disconnect/grounded system

### Amperage Rating

200 A

### Number of circuits

3

### Ground

Grounded

### Maximum voltage

1000 VDC

### NEMA rating

NEMA 4X

### Protection

Non-fusible

### Application

Solar

### Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

### System voltage

1000 VDC

### Voltage rating

1000 VDC

### Series

DC photovoltaic applications

### Enclosure

NEMA 4X

### Enclosure material

316 stainless steel

### Fuse configuration

Non-fusible

### Switch type

DC photovoltaic systems

Heavy duty

## Resources

### Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

### Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - DCG3104UXM](#)

Protection

Non-fusible



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)