

Eaton DCG4064URM

Catalog Number: DCG4064URM

Eaton heavy-duty DC disconnect,200A,Solar,Painted galvanized steel,Non-fusible,Grounded,In/Out(LC): 300 MCM-#6, In/Out(SR): 300 MCM-#6,600 Vdc,NEMA 3R,4,Non-fusible,Isolated return,Four-pole,DC photovoltaic applications,Single-throw

General specifications



Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCG4064URM

UPC

786685624907

Product Length/Depth

11.63 in

Product Height

35.38 in

Product Width

24.46 in

Product Weight

60 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 98B

NEC 690 per UL 1741

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

200 A

Number of circuits

4

Ground

Grounded

Maximum voltage

600 VDC

NEMA rating

NEMA 3R

Protection

Non-fusible

Application

Solar

Main lug wire size

In/Out(LC): 300 kcmil-#6, In/Out(SR): 300 kcmil-#6

Number of poles

Four-pole

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Isolation

Isolated return

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG4064URM](#)

Switch type

DC photovoltaic systems

Single-throw

Heavy duty safety

Protection

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)