

# Eaton DCG4065FWM

Catalog Number: DCG4065FWM

Eaton heavy-duty DC disconnect,400A,Solar,Grade 304 stainless steel,Fusible,Grounded,In/Out(LC): (1) 750 MCM-1/0 and (1) 600 MCM-#2, In/Out(SR): (2) 750 MCM-1/0,600 Vdc,NEMA 4X,4,Fusible,Four-pole,DC photovoltaic applications,Single-throw



## General specifications

### Product Name

Eaton heavy duty DC disconnect

### Catalog Number

DCG4065FWM

### UPC

786685865782

### Product Length/Depth

12.42 in

### Product Height

57.47 in

### Product Width

24.12 in

### Product Weight

131 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

DC disconnect/grounded system

### Amperage Rating

400 A

### Number of circuits

4

### Ground

Grounded

### Maximum voltage

600 VDC

### NEMA rating

NEMA 4X

### Protection

Fusible

### Application

Solar

### Main lug wire size

In/Out(LC): (1) 750 kcmil-1/0 and (1) 600 kcmil-#2, In/Out(SR):  
(2) 750 kcmil-1/0

### Number of poles

Four-pole

### System voltage

600 VDC per pole

### Voltage rating

600 VDC

### Series

DC photovoltaic applications

### Enclosure

NEMA 4X

### Enclosure material

304 stainless steel

### Fuse configuration

Fusible

### Switch type

DC photovoltaic systems

## Resources

### Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

### Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - DCG4065FWM](#)

Single-throw  
Heavy duty safety

Protection

Fusible



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)