

Eaton DCG6061UXM

Catalog Number: DCG6061UXM

Eaton heavy-duty DC disconnect,30A,Solar,Grade 316 stainless steel,Non-fusible,Grounded,In/Out(LC): #2-#14 AWG, In/Out(SR): 1/0-#14 AWG,600 Vdc,NEMA 4X,6,Non-fusible,Six-pole,DC photovoltaic applications,Single-throw



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCG6061UXM
UPC	Product Length/Depth
786685557366	10.22 in
Product Height	Product Width
19.08 in	12.88 in
Product Weight	Warranty
37 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
NEC 690 per UL 1741 UL 98B	Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

30 A

Number of circuits

6

Ground

Grounded

Maximum voltage

600 VDC

NEMA rating

NEMA 4X

Protection

Non-fusible

Application

Solar

Main lug wire size

In/Out(LC): #2-#14 AWG, In/Out(SR): 1/0-#14 AWG

Number of poles

Six-pole

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

316 stainless steel

Fuse configuration

Non-fusible

Switch type

DC photovoltaic systems

Heavy duty safety

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG6061UXM](#)

Single-throw

Protection

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia