

Eaton DCG6062FWM

Catalog Number: DCG6062FWM

Eaton heavy-duty DC disconnect,60A,Solar,Grade 304 stainless steel,Fusible,Grounded,In/Out(LC): #2-#14 AWG, In/Out(SR): 1/0-#14 AWG,600 Vdc,NEMA 4X,6,Fusible,Six-pole,DC photovoltaic applications,Single-throw



General specifications

Product Name

Eaton heavy duty DC disconnect

UPC

786685557342

Product Height

19.08 in

Product Weight

39 lb

Certifications

UL 98B
NEC 690 per UL 1741

Catalog Number

DCG6062FWM

Product Length/Depth

10.22 in

Product Width

12.88 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/grounded system

Amperage Rating

60 A

Number of circuits

6

Ground

Grounded

Maximum voltage

600 VDC

NEMA rating

NEMA 4X

Protection

Fusible

Application

Solar

Main lug wire size

In/Out(LC): #2-#14 AWG, In/Out(SR): 1/0-#14 AWG

Number of poles

Six-pole

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible

Switch type

Heavy duty safety

Single-throw

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCG6062FWM](#)

DC photovoltaic systems

Protection

Fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)