

Eaton DCU1063FXM

Catalog Number: DCU1063FXM

Eaton heavy duty DC disconnect,DC disconnect/ungrounded system,100A,NEMA 4X,Grade 316 stainless steel,Fusible,Ungrounded,#14-1/0 AWG lug capacity, #14-1/0 AWG solid return,600 Vdc,1,DC Photovoltaic Applications



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCU1063FXM
UPC	Product Length/Depth
786685557175	25.5 in
Product Height	Product Width
9 in	13.25 in
Product Weight	Warranty
27 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL 98B NEC 690 per UL 1741	Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

100 A

Number of circuits

1

Ground

Ungrounded

Maximum voltage

600 VDC

NEMA rating

NEMA 4X

Protection

Fusible

Application

Solar

Main lug wire size

#14-1/0 AWG lug capacity, #14-1/0 AWG solid return

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC Photovoltaic Applications

Enclosure

NEMA 4X

Enclosure material

316 stainless steel

Fuse configuration

Fusible

Switch type

Heavy duty

Protection

Fusible

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCU1063FXM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)