

Eaton DCU1101URM

Catalog Number: DCU1101URM

Eaton Heavy duty DC disconnect, 30 A, NEMA 3R, Painted galvanized steel, Non-fusible, Ungrounded, #14-#2 AWG lug capacity, #14-#2 AWG solid return, 1, DC photovoltaic applications, Rating:1000 Vdc



Photo is representative

General specifications

Product Name

Eaton heavy duty DC disconnect

UPC

786685557908

Product Height

8.5 in

Product Weight

6 lb

Catalog Number

DCU1101URM

Product Length/Depth

9.89 in

Product Width

8.87 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

NEC 690 per UL 1741
UL 98B

Catalog Notes

Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

30 A

Number of circuits

1

Ground

Ungrounded

Protection

Non-fusible

Application

Solar

Main lug wire size

#14-#2 AWG lug capacity, #14-#2 AWG solid return

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

Protection

Non-fusible

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCU1101URM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)