

Eaton DCU1102UXM

Catalog Number: DCU1102UXM

Eaton Heavy duty DC disconnect, 60 A, NEMA 4X, Grade 316 stainless steel, Non-fusible, Ungrounded, #14-#2 AWG lug capacity, #14-#2 AWG solid return, 1, DC photovoltaic applications, Rating:1000 Vdc



Photo is representative

General specifications

Product Name

Eaton heavy duty DC disconnect

UPC

786685558004

Product Height

14.14 in

Product Weight

21 lb

Certifications

NEC 690 per UL 1741

UL 98B

Catalog Number

DCU1102UXM

Product Length/Depth

10.22 in

Product Width

8.76 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

60 A

Number of circuits

1

Ground

Ungrounded

Protection

Non-fusible

Application

Solar

Main lug wire size

#14-#2 AWG lug capacity, #14-#2 AWG solid return

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

316 stainless steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

Protection

Non-fusible

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCU1102UXM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)