

Eaton DCU1104URM

Catalog Number: DCU1104URM

Eaton Heavy duty DC disconnect, 200 A, NEMA 3R, Stainless steel, Non-fusible, LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14, Max:1000 Vdc, NEMA 3R, 1, Non-fusible, System:1000 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCU1104URM
UPC	Product Length/Depth
786685625546	11.63 in
Product Height	Product Width
35.38 in	16.54 in
Product Weight	Warranty
45 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 98B
NEC 690 per UL 1741

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

200 A

Number of circuits

1

Maximum voltage

1000 VDC

NEMA rating

NEMA 3R

Protection

Non-fusible

Application

Solar

Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

Protection

Non-fusible

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DCU1104URM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)