

Eaton DCU1105FWM

Catalog Number: DCU1105FWM

Eaton Heavy duty DC disconnect, DCU, 400 A, DC photovoltaic systems, Grade 304 stainless steel, Fusible, Max:1000 Vdc, NEMA 4X, 1, Fusible



Photo is representative

General specifications

Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCU1105FWM

UPC

786685866239

Product Length/Depth

12.43 in

Product Height

57.47 in

Product Width

24.12 in

Product Weight

120.5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

400 A

Number of circuits

1

Maximum voltage

1000 VDC

NEMA rating

NEMA 4X

Protection

Fusible

Application

Solar

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible

Switch type

Heavy duty

Protection

Fusible

Resources

Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

Multimedia

Double Up on Safety

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - DCU1105FWM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)