

# Eaton DCU2064FRM

Catalog Number: DCU2064FRM

Eaton heavy duty DC disconnect,DC disconnect/ungrounded system,200A,NEMA 3R,Painted galvanized steel,Fusible,Ungrounded,LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14,600 Vdc,2



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty DC disconnect	DCU2064FRM
<b>UPC</b>	<b>Product Length/Depth</b>
786685625157	37.5 in
<b>Product Height</b>	<b>Product Width</b>
11.5 in	19 in
<b>Product Weight</b>	<b>Warranty</b>
45 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

NEC 690 per UL 1741  
UL 98B

## defaultTaxonomyAttributeLabel

### Type

DC disconnect/ungrounded system

### Amperage Rating

200 A

### Number of circuits

2

### Ground

Ungrounded

### Maximum voltage

600 VDC

### NEMA rating

NEMA 3R

### Protection

Fusible

### Application

Solar

### Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

### System voltage

600 VDC per pole

### Voltage rating

600 VDC

### Series

DC Photovoltaic Applications

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse configuration

Fusible

### Switch type

Heavy duty

### Protection

## Resources

### Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

### Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - DCU2064FRM](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)