

Eaton DCU2064UXM

Catalog Number: DCU2064UXM

Eaton heavy duty DC disconnect,DC disconnect/ungrounded system,200A,NEMA 4X,Grade 316 stainless steel,Non-fusible,Ungrounded,LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14,600 Vdc,2



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCU2064UXM
UPC	Product Length/Depth
786685625201	35.38 in
Product Height	Product Width
11.63 in	16.54 in
Product Weight	Warranty
45 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

NEC 690 per UL 1741
UL 98B

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

200 A

Number of circuits

2

Ground

Ungrounded

Maximum voltage

600 VDC

NEMA rating

NEMA 4X

Protection

Non-fusible

Application

Solar

Main lug wire size

LC: In 300 kcmil-#6 out 300 kcmil-#6. SR: in 300 kcmil-#6 out 300 kcmil-#6. EG: in #4-#14 AWG out 1/0-#14

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC Photovoltaic Applications

Enclosure

NEMA 4X

Enclosure material

316 stainless steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

Protection

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCU2064UXM](#)

Non-fusible



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)