

# Eaton DCU2065FRM

Catalog Number: DCU2065FRM

Eaton heavy duty DC disconnect,DC disconnect/ungrounded system,400A,NEMA 3R,Painted galvanized steel,Fusible,Ungrounded,600 Vdc,2,DC Photovoltaic Applications



## General specifications

### Product Name

Eaton heavy duty DC disconnect

### Catalog Number

DCU2065FRM

### UPC

786685865904

### Product Length/Depth

12.42 in

### Product Height

57.47 in

### Product Width

24.12 in

### Product Weight

118 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

DC disconnect/ungrounded system

### Amperage Rating

400 A

### Number of circuits

2

### Ground

Ungrounded

### Maximum voltage

600 VDC

### NEMA rating

NEMA 3R

### Protection

Fusible

### Application

Solar

### System voltage

600 VDC per pole

### Voltage rating

600 VDC

### Series

DC Photovoltaic Applications

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse configuration

Fusible

### Switch type

Heavy duty

### Protection

Fusible

## Resources

### Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

### Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

### Specifications and datasheets

[Eaton Specification Sheet - DCU2065FRM](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)