

Eaton DCU2065URM

Catalog Number: DCU2065URM

Eaton heavy duty DC disconnect,DC disconnect/ungrounded system,400A,NEMA 3R,Painted galvanized steel,Non-fusible,Ungrounded,600 Vdc,2,DC Photovoltaic Applications



General specifications

Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCU2065URM

UPC

786685865898

Product Length/Depth

12.42 in

Product Height

57.47 in

Product Width

24.12 in

Product Weight

115 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

400 A

Number of circuits

2

Ground

Ungrounded

Maximum voltage

600 VDC

NEMA rating

NEMA 3R

Protection

Non-fusible

Application

Solar

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC Photovoltaic Applications

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

Protection

Non-fusible

Resources

Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

Multimedia

Switching Devices Flex Center

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DCU2065URM

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)