

Eaton DCU2102UPM

Catalog Number: DCU2102UPM

Eaton Heavy duty DC disconnect, 60 A, NEMA 4, Painted steel, Non-fusible, Ungrounded, #14-#2 AWG lug capacity, #14-#2 AWG solid return, 2, DC photovoltaic applications, Rating:1000 Vdc



General specifications

Product Name

Eaton heavy duty DC disconnect

Catalog Number

DCU2102UPM

UPC

786685558066

Product Length/Depth

10.22 in

Product Height

19.08 in

Product Width

12.88 in

Product Weight

40 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

NEC 690 per UL 1741
UL 98B

Catalog Notes

Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Special features

For Ungrounded PV Systems

Type

DC disconnect/ungrounded system

Amperage Rating

60 A

Number of circuits

2

Ground

Ungrounded

Protection

Non-fusible

Application

Solar

Main lug wire size

#14-#2 AWG lug capacity, #14-#2 AWG solid return

System voltage

1000 VDC

Voltage rating

1000 VDC

Series

DC photovoltaic applications

Enclosure

NEMA 4

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

Protection

Non-fusible

Resources

Brochures

DC disconnects for grounded and ungrounded photovoltaic installations

Multimedia

Double Up on Safety

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - DCU2102UPM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)