

Eaton DCU3062UWM

Catalog Number: DCU3062UWM

Eaton heavy duty DC disconnect,DC disconnect/ungrounded system,60A,NEMA 4X,Grade 304 stainless steel,Non-fusible,Ungrounded,#14-#2 AWG lug capacity, #14-1/0 AWG solid return,600 Vdc,3,DC Photovoltaic Applications



General specifications

Product Name	Catalog Number
Eaton heavy duty DC disconnect	DCU3062UWM
UPC	Product Length/Depth
786685557557	10.22 in
Product Height	Product Width
19.08 in	12.88 in
Product Weight	Warranty
37 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
NEC 690 per UL 1741 UL 98B	Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

defaultTaxonomyAttributeLabel

Type

DC disconnect/ungrounded system

Amperage Rating

60 A

Number of circuits

3

Ground

Ungrounded

Maximum voltage

600 VDC

NEMA rating

NEMA 4X

Protection

Non-fusible

Application

Solar

Main lug wire size

#14-#2 AWG lug capacity, #14-1/0 AWG solid return

System voltage

600 VDC per pole

Voltage rating

600 VDC

Series

DC Photovoltaic Applications

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Non-fusible

Switch type

Heavy duty

Protection

Non-fusible

Resources

Brochures

[DC disconnects for grounded and ungrounded photovoltaic installations](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DCU3062UWM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)