

Eaton DD322NWKW-00V2

Catalog Number: DD322NWKW-00V2

Eaton Double door single-throw fused safety switch, Voltage indicator load side, 60 A, NEMA 4X, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 20, 25/ 30, 50 hp (1/3PH @480, 600 V), #14-#2



General specifications

Product Name

Eaton double door single-throw fused safety switch

Catalog Number

DD322NWKW-00V2

UPC

786679176962

Product Length/Depth

37.49 in

Product Height

8.22 in

Product Width

12.33 in

Product Weight

37 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Double Door Isolation Switch w/ Load Side Voltage Indicator

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty double door safety switch

Wire size

#14-2 AWG

Resources

Multimedia

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Double Door Line Isolation Safety Switch](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DD322NWKW-00V2](#)

Performance Ratings

Amperage Rating

60A

Fuse class provision

Class H

HP rating - max

20, 25/ 30, 50 hp (1/3PH @480, 600 V)

NEMA rating

NEMA 4X

Voltage rating

240V

Miscellaneous

Product Category

Watertight

Special features

V indicator load side, w/ window



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)