

Eaton DD323FDKW

Catalog Number: DD323FDKW

Eaton Double door single-throw fused safety switch, 100 A, NEMA 12/3R, Fusible without neutral, Three-pole, Three-wire, 240 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0

General specifications

Product Name

Eaton double door single-throw fused safety switch

Catalog Number

DD323FDKW

UPC

786679173114

Product Length/Depth

39.19 in

Product Height

10.21 in

Product Width

12.33 in

Product Weight

50 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Double Door Isolation Switch



Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty double door safety switch

Wire size

#14-1/0 AWG

Resources

Multimedia

[Double Door Line Isolation Safety Switch](#)

[Switching Devices Flex Center](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Eaton Specification Sheet - DD323FDKW](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Performance Ratings

Amperage Rating

100A

Fuse class provision

Class H

HP rating - max

30, 40/ 60, 75 hp (1/3PH @480, 600 V)

Voltage rating

240V

Miscellaneous

Product Category

Dust tight

Special features

w/ window



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)