

Eaton DD325FDKW-00V2

Catalog Number: DD325FDKW-00V2

Eaton Double door single-throw fused safety switch, Voltage indicator load side, 400 A, NEMA 12/3R, w/out neutral, Three-pole, Three-wire, 240 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0(1)#1/0-(2)300 kcmil-#1/0, or (1)175 kcmil-#1/0

General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD325FDKW-00V2
	UPC
	786679184073
Product Length/Depth	Product Height
16.41 in	24.32 in
Product Width	Product Weight
72.46 in	219 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	



Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty double door safety switch

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class H

HP rating - max

250, 350 hp (3PH @480/600 V)

Voltage rating

240V

Miscellaneous

Product Category

Dust tight

Special features

V indicator load side, w/ window

Resources

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[Double Door Line Isolation Safety Switch](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Eaton Specification Sheet - DD325FDKW-00V2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)