

Eaton DD325NWKW

Catalog Number: DD325NWKW

Eaton Double door single-throw fused safety switch, 400 A, NEMA 4X, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0(1)#1/0-(2)300 kcmil-#1/0, or (1)175 kcmil-#1/0



General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD325NWKW
	UPC
	786679184226
Product Length/Depth	Product Height
16.41 in	24.32 in
Product Width	Product Weight
72.46 in	219 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty double door safety switch

Resources

Multimedia

[Double Door Line Isolation Safety Switch](#)

[Switching Devices Flex Center](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DD325NWKW](#)

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class H

HP rating - max

250, 350 hp (3PH @480/600 V)

Voltage rating

240V

Miscellaneous

Product Category

Watertight

Special features

w/ window



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)