

Eaton DD327NDKW-00V2

Catalog Number: DD327NDKW-00V2

Eaton Double door single-throw fused safety switch, Voltage indicator load side, 800 A, NEMA 12/3R, Class L, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 500, 500 hp (3PH @480/600 V), (4)#1/0-(4)750 kcmil

General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD327NDKW-00V2
	UPC
	786679173756
Product Length/Depth	Product Height
86.73 in	22.16 in
Product Width	Product Weight
26.57 in	300 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Double Door Isolation Switch w/ Load Side Voltage Indicator



Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty double door safety switch

Performance Ratings

Amperage Rating

800A

Fuse class provision

Class L

HP rating - max

500, 500 hp (3PH @480/600 V)

Voltage rating

240V

Miscellaneous

Product Category

Dust tight

Special features

V indicator load side, w/ window

Resources

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

[Double Door Line Isolation Safety Switch](#)

[ARMS Enclosed Circuit Breaker](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

Specifications and datasheets

[Eaton Specification Sheet - DD327NDKW-00V2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)