

Eaton DD328FDKW

Catalog Number: DD328FDKW

Eaton Double door single-throw fused safety switch, 1200 A, NEMA 12/3R, Painted galvanized steel, Class L, Fusible without neutral, Three-pole, Three-wire, 240 V, Max Hp: 500, 500 hp (3PH @480/600 V), (4)#1/0-(4)750 kcmil

General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD328FDKW
	UPC
	786679184028
Product Length/Depth	Product Height
27.18 in	43.11 in
Product Width	Product Weight
91.02 in	575 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	



Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty double door safety switch

Performance Ratings

Amperage Rating

1200A

Fuse class provision

Class L

HP rating - max

500, 500 hp (3PH @480/600 V)

Voltage rating

240V

Miscellaneous

Product Category

Dust tight

Special features

w/ window

Resources

Multimedia

[Double Up on Safety](#)

[Double Door Line Isolation Safety Switch](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[ARMS Enclosed Circuit Breaker](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DD328FDKW](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)