

Eaton DD361NWKW-00V1

Catalog Number: DD361NWKW-00V1

Eaton Double door single-throw fused safety switch, Voltage indicator line side, 30 A, NEMA 4X, 304 stainless steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 7.5, 10/15, 20 hp (1/3PH @480, 600 V), #14-#2



General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD361NWKW-00V1
	UPC
	786679177358
Product Length/Depth	Product Height
37.49 in	8.22 in
Product Width	Product Weight
12.33 in	37 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Double Door Isolation Switch w/ Line Side Voltage Indicator

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty double door safety switch

Wire size

#14-2 AWG

Resources

Multimedia

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[ARMS Enclosed Circuit Breaker](#)

[Switching Devices Flex Center](#)

[Double Door Line Isolation Safety Switch](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DD361NWKW-00V1](#)

Performance Ratings

Amperage Rating

30A

Fuse class provision

Class H

HP rating - max

7.5, 10/ 15, 20 hp (1/3PH @480, 600 V)

NEMA rating

NEMA 4X

Voltage rating

600 V

Miscellaneous

Product Category

Watertight

Special features

V indicator line side, w/ window



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)