

Eaton DD363NWKW-00V1

Catalog Number: DD363NWKW-00V1

Eaton Double door single-throw fused safety switch, Voltage indicator line side, 100 A, NEMA 4X, 304 stainless steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 30, 40/60, 75 hp (1/3PH @480, 600 V), #14-#1/0



General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD363NWKW-00V1
	UPC
	786679173923
Product Length/Depth	Product Height
39.19 in	10.21 in
Product Width	Product Weight
12.33 in	50 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty double door safety switch

Wire size

#14-1/0 AWG

Performance Ratings

Amperage Rating

100A

Fuse class provision

Class H

HP rating - max

30, 40/ 60, 75 hp (1/3PH @480, 600 V)

NEMA rating

NEMA 4X

Voltage rating

600 V

Miscellaneous

Product Category

Watertight

Special features

V indicator line side, w/ window

Resources

Multimedia

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

[Double Door Line Isolation Safety Switch](#)

Specifications and datasheets

[Eaton Specification Sheet - DD363NWKW-00V1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)