

Eaton DD364NDKW-00V3

Catalog Number: DD364NDKW-00V3

Eaton Double door single-throw fused safety switch, Voltage indicator line and load side, 200 A, NEMA 12/3R, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 50, 50/ 125, 150 hp (1/3PH @480, 600 V), #6-300 kcmil

General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD364NDKW-00V3
	UPC
	786679174432
Product Length/Depth	Product Height
49.9 in	11.62 in
Product Width	Product Weight
17.18 in	85 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	



Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty double door safety switch

Performance Ratings

Amperage Rating

200A

Fuse class provision

Class H

HP rating - max

50, 50/ 125, 150 hp (1/3PH @480, 600 V)

NEMA rating

NEMA 12

Voltage rating

600 V

Miscellaneous

Product Category

Dust tight

Special features

V indicator line and load side, w/ window

Resources

Multimedia

[Double Door Line Isolation Safety Switch](#)

[Switching Devices Flex Center](#)

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

Specifications and datasheets

[Eaton Specification Sheet - DD364NDKW-00V3](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)