

Eaton DD365FWKW

Catalog Number: DD365FWKW

Eaton Double door single-throw fused safety switch, 400 A, NEMA 4X, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0(1)#1/0-(2)300 kcmil-#1/0, or (1)175 kcmil-#1/0



General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD365FWKW
	UPC
	786679184585
Product Length/Depth	Product Height
16.41 in	24.32 in
Product Width	Product Weight
72.46 in	219 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty double door safety switch

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class H

HP rating - max

250, 350 hp (3PH @480/600 V)

Voltage rating

600 V

Miscellaneous

Product Category

Watertight

Special features

w/ window

Resources

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[Double Door Line Isolation Safety Switch](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DD365FWKW](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)