

Eaton DD366FWKW-00V2

Catalog Number: DD366FWKW-00V2

Eaton Double door single-throw fused safety switch, Voltage indicator load side, 600 A, NEMA 4X, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 400, 500 hp (3PH @480/600 V), (1)#2(1)#2-(1)600, and (1)750 kcmil



General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD366FWKW-00V2
	UPC
	786679184738
Product Length/Depth	Product Height
19.31 in	25.32 in
Product Width	Product Weight
77.96 in	265 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty double door safety switch

Performance Ratings

Amperage Rating

600A

Fuse class provision

Class H

HP rating - max

400, 500 hp (3PH @480/600 V)

Voltage rating

600 V

Miscellaneous

Product Category

Watertight

Special features

V indicator load side, w/ window

Resources

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[Switching Devices Flex Center](#)

[Double Door Line Isolation Safety Switch](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DD366FWKW-00V2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)