

Eaton DD367NWKW-00V1

Catalog Number: DD367NWKW-00V1

Eaton Double door single-throw fused safety switch, Voltage indicator line side, 800 A, NEMA 4X, 304 stainless steel, Class L, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 500, 500 hp (3PH @480/600 V), (4)#1/0-(4)750 kcmil



General specifications

Product Name	Catalog Number
Eaton double door single-throw fused safety switch	DD367NWKW-00V1
	UPC
	786679174616
Product Length/Depth	Product Height
86.73 in	22.16 in
Product Width	Product Weight
26.57 in	300 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty double door safety switch

Performance Ratings

Amperage Rating

800A

Fuse class provision

Class L

HP rating - max

500, 500 hp (3PH @480/600 V)

NEMA rating

NEMA 4X

Voltage rating

600 V

Miscellaneous

Product Category

Watertight

Special features

V indicator line side, w/ window

Resources

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Flex Center Customized Double Door Switch with Voltage Indicator and Safe-Test Point](#)

[Switching Devices Flex Center](#)

[Double Door Line Isolation Safety Switch](#)

Specifications and datasheets

[Eaton Specification Sheet - DD367NWKW-00V1](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)