

Eaton DF10P-C2

Catalog Number: DF10P-C2

Eaton 0-10V decorator dimmer, Preset feature, #14 – 12 AWG, 120/277V, Back and side wiring, Slide actuator, light almond, white, ivory, 1000 sq ft coverage illumination, LED, FLR, single-pole, three-way, 1200W, 1660W, 736834

General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DF10P-C2
UPC	Product Length/Depth
032664736834	2.1 in
Product Height	Product Width
5.9 in	3.8 in
Product Weight	Certifications
0.001 lb	cULus Listed
	NOM

defaultTaxonomyAttributeLabel

Frequency rating

60 Hz

Special features

Preset feature

Type

Dimmer

Voltage rating

120/277 V

Power consumption

1660 W

1200 W

Illumination

1000 sq ft coverage

Wiring method

Back and side

Environmental conditions

Indoor

Switch type

Single-pole, three-way

Load type

FLR

LED

Torque rating

14 lbf-inch

Actuator

Slide

Color

Ivory

White

Light almond

Connection type

Screw terminal

Resources

Installation videos

[How to install Eaton's universal slide dimmers](#)

Specifications and datasheets

[Eaton Specification Sheet - DF10P-C2](#)

[Decorator 0-10 volt dimmer spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)