

# Eaton DF10P-C4

Catalog Number: DF10P-C4

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120/277V, Bck and sd wiring, Slide actuator, Black, wht, ivory, 1000 sq ft coverage illumination, LED, FLR, 1-pole, 3-way, 1200W, 1660W 736841



## General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DF10P-C4
UPC	Product Length/Depth
032664736841	2.1 in
Product Height	Product Width
5.9 in	3.8 in
Product Weight	Certifications
0.001 lb	NOM
	cULus Listed

## defaultTaxonomyAttributeLabel

### Frequency rating

60 Hz

### Special features

Preset feature

### Type

Dimmer

### Voltage rating

120/277 V

### Power consumption

1660 W

1200 W

### Illumination

1000 sq ft coverage

### Wiring method

Back and side

### Environmental conditions

Indoor

### Switch type

Single-pole, three-way

### Load type

FLR

LED

### Torque rating

14 lbf-inch

### Actuator

Slide

### Color

Ivory

White

Black

### Connection type

Screw terminal

## Resources

### Installation videos

[How to install Eaton's universal slide dimmers](#)

### Specifications and datasheets

[Eaton Specification Sheet - DF10P-C4](#)

[Decorator 0-10 volt dimmer spec sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)