

Eaton DH261FRK

Catalog Number: DH261FRK

Eaton Heavy duty single-throw fused safety switch, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Two-pole, Two-wire, 600 V, Max Hp: 7.5, 10 hp/15 hp (1PH @480,600 V TD/600 Vdc), #14-#2 Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH261FRK
UPC	Product Length/Depth
786685177120	17 in
Product Height	Product Width
7.75 in	9.5 in
Product Weight	Warranty
17 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	
CSA Certified	

Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Two-pole

Number of wires

2

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

30A

HP rating - max

7.5, 10 hp/15 hp (1PH @480,600 V TD/600 Vdc)

NEMA rating

NEMA 3R

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH261FRK



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia