

Eaton DI10P-LA

Catalog Number: DI10P-LA

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Lt almd, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 1000W 662423



General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DI10P-LA
UPC	Product Length/Depth
032664662423	2.063 in
Product Height	Product Width
4.375 in	3.125 in
Product Weight	Certifications
0.001 lb	cULus Listed NOM

defaultTaxonomyAttributeLabel

Frequency rating

60 Hz

Special features

Preset feature

Type

Dimmer

Voltage rating

120 V

Power consumption

1000 W

Wiring method

Back and side

Environmental conditions

Indoor

Switch type

Single-pole, three-way

Load type

MLV

HAL

INC

Housing

Polycarbonate

Torque rating

14 lbf-inch

Material

Polycarbonate

Actuator

Slide

Color

Light almond

Connection type

Wire lead

Resources

Brochures

[Lighting controls line card brochure](#)

Installation videos

[How to install Eaton's universal slide dimmers](#)

Specifications and datasheets

[Eaton Specification Sheet - DI10P-LA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)