

Eaton DILM12-21(24VDC)

Catalog Number: DILM12-21(24VDC)

Eaton XT IEC mini contactor, 12A, 24 Vdc, 2NO-1NC, 12A, Frame B, 45 mm, 1, 2/ 3, 3, 10, 10 (1/3PH @120, 240/208, 240, 480, 600 V), Three-pole, Non-reversing, Screw terminals, FVNR, 5.5 kW

General specifications



Photo is representative

Product Name

Eaton XT IEC mini contactor

Catalog Number

DILM12-21(24VDC)

EAN

4015082769154

Product Length/Depth

1.8 in

Product Height

2.7 in

Product Width

4.9 in

Product Weight

0.78 lb

Warranty

1 year

Compliances

CE Marked

RoHS Compliant

Certifications

CSA Certified

IEC 60947

EN 60947

UL Listed

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

12A

HP rating - max

1, 2/ 3, 3, 10, 10 (1/3PH @120,240/208,240,480,600 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing miniature contactor

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vdc

Coil voltage

24 Vdc

Contact configuration

2 NO, 1 NC

Continuous ampere rating

12 A

Series

XT IEC

Operation

Non-reversing

Power consumption

5.5 kW

Resources

Multimedia

S1. E4. Ask the Experts - NEMA, IEC and DP contactors

Contactors Explained

Specifications and datasheets

Global Data Sheet - DILM12-21(24VDC)

Eaton Specification Sheet - DILM12-21(24VDC)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)